

LipuJet-P-RA Extension stage 3

Product information for the product group




ACO Product benefits

- Easy to transport and fit thanks delivery of individual parts
 - Odour-free emptying, cleaning and filling
 - Pre- and post-cleaning times can be set individually
 - Hydromechanical high-pressure cleaning – only a cold-water connection required
 - Can be equipped with an disposal pump
 - Small delivery dimensions
 - Low weight
- Grease separator plant as per DIN EN 1825 and DIN 4040-100
 - For indoors installation – frost free
 - With integrated sludge trap
 - Operating side: right/left
 - Draining connection, fire hose quick coupling B 2½"
 - Suction and emptying sump with drain plug socket 1½"
- Inspection window with wiper
 - Automatic high-pressure internal cleaning with pump
 - Nominal pressure: 175 bar
 - Capacity: 13 l/min
 - Chopping, mixing, rinsing in one process
 - Standard control with group fault reporting
- Odour-proof maintenance opening, diameter: 350 mm
 - Filling device with magnetic valve (connection ¾") for automatic refilling
 - Electrical connector: 400 V/50 Hz/16 A/3,9 kW
 - System ACO Passavant
 - Building Supervisory Authority approval Z-54.1-491

Item Technical Data 3504.73.32





Nominal capacity	Nominal width	Contents			Weight			Operation side
		Sludge trap	Grease store	Overall	Empty	Full	Heaviest single component	
		[l]	[l]	[l]	[kg]	[kg]	[kg]	
NS 4	DN 100	500	160	890	181	1071	55	Left-hand

Dimensions



Nominal capacity	Dimensions												
	L1	L2	L3	L4	L5	H1	H2	H3	H4	H5	D	D1	Z/Anzahl Segmente
	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	
NS 4	1255	60	200	65	260	1240	1170	1580	1630	1830	110	1150	820/2

Accessories

	Description	Used with	Description	Item number
	Sampling pot DN 100	<ul style="list-style-type: none"> ■ Grease separator LipuJet-P/LipuSmart-P <ul style="list-style-type: none"> □ NS 1 – 4 ■ Starch separator FapuJet-P-OAP <ul style="list-style-type: none"> □ NS 0.5 – 1 	<ul style="list-style-type: none"> ■ For installation of horizontal pipes DN 100 to grease separator ■ Round shape with <ul style="list-style-type: none"> □ Coupling socket seal (material SBR) on inlet and spigot on outflow □ Odour-proof maintenance opening DN 450 ■ Weight: 10.2 kg 	3300.09.11
	Sampling pot DN 100	<ul style="list-style-type: none"> ■ Grease separator LipuJet-P/LipuSmart-P <ul style="list-style-type: none"> □ NS 1 – 4 ■ Starch separator FapuJet-P-OAP <ul style="list-style-type: none"> □ NS 0.5 – 1 	<ul style="list-style-type: none"> ■ For installation in vertical pipes DN 100 going to grease separator ■ Round shape with <ul style="list-style-type: none"> □ Coupling socket seal (material SBR) on inlet and spigot on outflow □ Odour-proof maintenance opening DN 450 ■ Weight: 10.2 kg 	3300.10.11
	Viewing window	<ul style="list-style-type: none"> ■ Grease separator <ul style="list-style-type: none"> □ LipuJet-P-OB/OD/R/RD □ LipuSmart-P-OB/OD ■ BioJet-P-OM/RM (NS 2-25) 	<ul style="list-style-type: none"> ■ Nominal width: DN 200 ■ With screen wiper ■ Weight: 3.2 kg 	3300.11.10
	Filling device	<ul style="list-style-type: none"> ■ Grease separator <ul style="list-style-type: none"> □ LipuJet-P-OB/OD/R/RD □ LipuSmart-P-OB/OD ■ BioJet-P-OM/RM (NS 2-25) 	<ul style="list-style-type: none"> ■ Free outlet as per DIN 1988 Part 4 ■ For connection to drinking water supply ■ With ball valve R 3/4" ■ With pressure relief valve ■ Weight: 3.5 kg 	3300.11.22

	Description	Used with	Description	Item number
	Grease layer thickness measuring device	<ul style="list-style-type: none"> ■ LipuJet-P <ul style="list-style-type: none"> □ Oval NS 1 – 10 □ Round NS 2 – 20 ■ LipuJet-S <ul style="list-style-type: none"> □ Oval NS 1 – 10 □ Round NS 2 – 20 ■ LipuSmart-P <ul style="list-style-type: none"> □ Oval NS 1 – 10 	<ul style="list-style-type: none"> ■ For electronic measurement of layer of grease ■ Suitable for liquid and/or congealing grease ■ Measuring device with plug and used connecting cable, length: 3 m ■ With two voltage-free changeover contacts to display full warning (80 %) and advance warning of fill level (50 %) ■ With visual display of fill level ■ With heated probe rod to increase reliability of operation ■ Operating voltage: 230VAC/5 VA ■ Max consumption approx. 12 W ■ Weight: 2.8 kg 	3300.11.50

You can find further accessories under → [/35047332](#)