

**LipuJet-P-RAP Extension stage 3**

**Product information for the product group**



**ACO Product benefits**

- Easy to transport and fit thanks delivery of individual parts
- Odour-free emptying, cleaning and filling
- Pre- and post-cleaning times can be set individually
- Hydromechanical high-pressure cleaning – only a cold-water connection required
- Small delivery dimensions
- Low weight

- Grease separator plant as per DIN EN 1825 and DIN 4040-100
- For indoors installation – frost free
- With integrated sludge trap
- Operating side: right/left
- Draining connection, fire hose quick coupling B 2½"
- Suction and emptying sump with drain plug socket 1½"
- Inspection window with wiper

- Automatic high-pressure internal cleaning with pump
  - Nominal pressure: 175 bar
  - Capacity: 13 l/min
  - Chopping, mixing, rinsing in one process
- Standard control with group fault reporting
- Disposal pump with free flow impeller
  - Motor power: 3.0 kW/2850 rpm
  - Delivery performance: 20 m³/h at 1 bar medium delivery head
- Stop valve upstream of disposal pump


- Odour-proof maintenance opening, diameter: 350 mm
- Filling device with magnetic valve (connection ¾") for automatic refilling
- Electrical connector: 400 V/50 Hz/16 A/6,9 kW
- System ACO Passavant
  - Building Supervisory Authority approval Z-54.1-491

**Item Technical Data 3520.73.72**

Nominal capacity	Nominal width	Contents			Empty	Weight		Operation side
		Sludge trap	Grease store	Overall		Full	Heaviest single component	
		[l]	[l]	[l]	[kg]	[kg]	[kg]	
NS 20	DN 200	2440	800	4070	443	4513	134	Left-hand





ACO eServices on the Internet:


Dimensions



Nominal capacity	Dimensions														
	L1	L2	L3	L4	L5	L6	H1	H2	H3	H4	H5	D	D1	Z/Anzahl Segmente	
	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]		
NS 20	2130	60	150	520	65	260	1955	1855	2400	2450	2650	200	1920	880/3	

## Accessories

	Description	Used with	Description	Item number
	Sampling pot DN 200	<ul style="list-style-type: none"> <li>■ Grease separator LipuJet-P                             <ul style="list-style-type: none"> <li>□ NS 15 – 20</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>■ For installation of horizontal pipes DN 200 to grease separator</li> <li>■ Round shape with                             <ul style="list-style-type: none"> <li>□ Coupling socket seal (material SBR) on inlet and spigot on outflow</li> <li>□ Odour-proof maintenance opening DN 450</li> </ul> </li> <li>■ Weight: 10.3 kg</li> </ul>	<b>3300.09.31</b>
	Sampling pot DN 200	<ul style="list-style-type: none"> <li>■ Grease separator LipuJet-P                             <ul style="list-style-type: none"> <li>□ NS 15 – 20</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>■ For installation in vertical pipes DN 200 going to grease separator</li> <li>■ Round shape with                             <ul style="list-style-type: none"> <li>□ Coupling socket seal (material SBR) on inlet and spigot on outflow</li> <li>□ Odour-proof maintenance opening DN 450</li> </ul> </li> <li>■ Weight: 10.2 kg</li> </ul>	<b>3300.10.31</b>
	Viewing window	<ul style="list-style-type: none"> <li>■ Grease separator                             <ul style="list-style-type: none"> <li>□ LipuJet-P-OB/OD/R/RD</li> <li>□ LipuSmart-P-OB/OD</li> </ul> </li> <li>■ BioJet-P-OM/RM (NS 2-25)</li> </ul>	<ul style="list-style-type: none"> <li>■ Nominal width: DN 200</li> <li>■ With screen wiper</li> <li>■ Weight: 3.2 kg</li> </ul>	<b>3300.11.10</b>
	Filling device	<ul style="list-style-type: none"> <li>■ Grease separator                             <ul style="list-style-type: none"> <li>□ LipuJet-P-OB/OD/R/RD</li> <li>□ LipuSmart-P-OB/OD</li> </ul> </li> <li>■ BioJet-P-OM/RM (NS 2-25)</li> </ul>	<ul style="list-style-type: none"> <li>■ Free outlet as per DIN 1988 Part 4</li> <li>■ For connection to drinking water supply</li> <li>■ With ball valve R ¾"</li> <li>■ With pressure relief valve</li> <li>■ Weight: 3.5 kg</li> </ul>	<b>3300.11.22</b>

	Description	Used with	Description	Item number
	<p>Grease layer thickness measuring device</p>	<ul style="list-style-type: none"> <li>■ LipuJet-P                             <ul style="list-style-type: none"> <li>□ Oval NS 1 – 10</li> <li>□ Round NS 2 – 20</li> </ul> </li> <li>■ LipuJet-S                             <ul style="list-style-type: none"> <li>□ Oval NS 1 – 10</li> <li>□ Round NS 2 – 20</li> </ul> </li> <li>■ LipuSmart-P                             <ul style="list-style-type: none"> <li>□ Oval NS 1 – 10</li> </ul> </li> </ul>	<ul style="list-style-type: none"> <li>■ For electronic measurement of layer of grease</li> <li>■ Suitable for liquid and/or congealing grease</li> <li>■ Measuring device with plug and used connecting cable, length: 3 m</li> <li>■ With two voltage-free changeover contacts to display full warning (80 %) and advance warning of fill level (50 %)</li> <li>■ With visual display of fill level</li> <li>■ With heated probe rod to increase reliability of operation</li> <li>■ Operating voltage: 230VAC/5 VA</li> <li>■ Max consumption approx. 12 W</li> <li>■ Weight: 2.8 kg</li> </ul>	<p><b>3300.11.50</b></p>

You can find further accessories under → [/35207372](#)

