

LipuJet-P-RAP Extension stage 3

Product information for the product group



ACO Product benefits

- Easy to transport and fit thanks delivery of individual parts
- Odour-free emptying, cleaning and filling
- Pre- and post-cleaning times can be set individually
- Hydromechanical high-pressure cleaning – only a cold-water connection required
- Small delivery dimensions
- Low weight

- Grease separator plant as per DIN EN 1825 and DIN 4040-100
- For indoors installation – frost free
- With integrated sludge trap
- Operating side: right/left
- Draining connection, fire hose quick coupling B 2½"
- Suction and emptying sump with drain plug socket 1½"
- Inspection window with wiper

- Automatic high-pressure internal cleaning with pump
 - Nominal pressure: 175 bar
 - Capacity: 13 l/min
 - Chopping, mixing, rinsing in one process
- Standard control with group fault reporting
- Disposal pump with free flow impeller
 - Motor power: 3.0 kW/2850 rpm
 - Delivery performance: 20 m³/h at 1 bar medium delivery head
- Stop valve upstream of disposal pump


- Odour-proof maintenance opening, diameter: 350 mm
- Filling device with magnetic valve (connection ¾") for automatic refilling
- Electrical connector: 400 V/50 Hz/16 A/6,9 kW
- System ACO Passavant
 - Building Supervisory Authority approval Z-54.1-491

Item Technical Data 3507.73.72

Nominal capacity	Nominal width	Contents			Empty	Weight		Operation side
		Sludge trap	Grease store	Overall		Full	Heaviest single component	
		[l]	[l]	[l]	[kg]	[kg]	[kg]	
NS 7	DN 150	830	400	2120	382	2502	112	Left-hand





ACO eServices on the Internet:


Dimensions



Nominal capacity	Dimensions														
	L1	L2	L3	L4	L5	L6	H1	H2	H3	H4	H5	D	D1	Z/Anzahl Segmente	
	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]	[mm]		
NS 7	1820	60	150	520	65	260	1430	1330	1880	1930	2130	160	1660	785/3	

Accessories

	Description	Used with	Description	Item number
	Sampling pot DN 150	<ul style="list-style-type: none"> ■ Grease separator LipuJet-P/LipuSmart-P <ul style="list-style-type: none"> □ NS 5.5 – 10 ■ Starch separator FapuJet-P-OAP <ul style="list-style-type: none"> □ NS 2 	<ul style="list-style-type: none"> ■ For installation of horizontal pipes DN 150 to grease separator ■ Round shape with <ul style="list-style-type: none"> □ Coupling socket seal (material SBR) on inlet and spigot on outflow □ Odour-proof maintenance opening DN 450 ■ Weight: 10.1 kg 	3300.09.21
	Sampling pot DN 150	<ul style="list-style-type: none"> ■ Grease separator LipuJet-P/LipuSmart-P <ul style="list-style-type: none"> □ NS 5.5 – 10 ■ Starch separator FapuJet-P-OAP <ul style="list-style-type: none"> □ NS 2 	<ul style="list-style-type: none"> ■ For installation in vertical pipes DN 150 going to grease separator ■ Round shape with <ul style="list-style-type: none"> □ Coupling socket seal (material SBR) on inlet and spigot on outflow □ Odour-proof maintenance opening DN 450 ■ Weight: 10.1 kg 	3300.10.21
	Viewing window	<ul style="list-style-type: none"> ■ Grease separator <ul style="list-style-type: none"> □ LipuJet-P-OB/OD/R/RD □ LipuSmart-P-OB/OD ■ BioJet-P-OM/RM (NS 2-25) 	<ul style="list-style-type: none"> ■ Nominal width: DN 200 ■ With screen wiper ■ Weight: 3.2 kg 	3300.11.10
	Filling device	<ul style="list-style-type: none"> ■ Grease separator <ul style="list-style-type: none"> □ LipuJet-P-OB/OD/R/RD □ LipuSmart-P-OB/OD ■ BioJet-P-OM/RM (NS 2-25) 	<ul style="list-style-type: none"> ■ Free outlet as per DIN 1988 Part 4 ■ For connection to drinking water supply ■ With ball valve R ¾" ■ With pressure relief valve ■ Weight: 3.5 kg 	3300.11.22

	Description	Used with	Description	Item number
	<p>Grease layer thickness measuring device</p>	<ul style="list-style-type: none"> ■ LipuJet-P <ul style="list-style-type: none"> □ Oval NS 1 – 10 □ Round NS 2 – 20 ■ LipuJet-S <ul style="list-style-type: none"> □ Oval NS 1 – 10 □ Round NS 2 – 20 ■ LipuSmart-P <ul style="list-style-type: none"> □ Oval NS 1 – 10 	<ul style="list-style-type: none"> ■ For electronic measurement of layer of grease ■ Suitable for liquid and/or congealing grease ■ Measuring device with plug and used connecting cable, length: 3 m ■ With two voltage-free changeover contacts to display full warning (80 %) and advance warning of fill level (50 %) ■ With visual display of fill level ■ With heated probe rod to increase reliability of operation ■ Operating voltage: 230VAC/5 VA ■ Max consumption approx. 12 W ■ Weight: 2.8 kg 	<p>3300.11.50</p>

You can find further accessories under → [/35077372](#)

